

# MX Analytical Balances

## Fast and Accurate



### Fast and Accurate Weighing

The high-resolution load cell delivers accurate and reliable results and offers readability as low as 0.01 mg. With the SmartPan, the balance stabilizes quickly, even in turbulent environments, enabling fast and efficient weighing.



### GxP Compliance Support

Automatic data logging and user management options help you to comply with GxP guidelines. Transfer data to a printer or computer for complete and error-free documentation.



### Innovative Engineering

Clever features provide an ergonomic, stress-free weighing experience, especially for long or repetitive tasks: The StatusLight provides instant confirmation of the balance status, the backlit draft shield offers high visibility, and the ErgoDoors make weighing convenient.



### Sustainable Design

High-quality materials and robust construction ensure a long balance lifetime, providing an overall low cost of ownership. Designed with sustainability in mind, including a power-saving mode, MX balances are efficient and economical in operation.



### Smart Features

#### For Advanced Requirements

The superior load cell, quality assurance functions, and multiple connectivity options combine to satisfy higher demands for accuracy, compliance, and efficiency. Easily integrated into your existing laboratory infrastructure, these balances have a multitude of smart features to make your weighing processes fast, convenient, and efficient.

Define your own routine testing schedule on the balance according to your internal quality requirements and process tolerances. Your balance will remind you when tests are due to be sure your results remain accurate in the intervals between calibrations.

## Technical Specifications



	MX105	MX105DU	MX205DU
<b>Limit values</b>			
Capacity	120 g	120 g	220 g
Readability	0.01 mg	0.1 mg	0.1 mg
Capacity of fine range	–	42 g	82 g
Readability in fine range	–	0.01 mg	0.01 mg
Repeatability (at 5% load)	0.02 mg	0.02 mg	0.02 mg
Linearity deviation	0.1 mg	0.2 mg	0.2 mg
Sensitivity offset (at nominal load) ▲	0.4 mg	0.4 mg	0.8 mg
<b>Typical values</b>			
Repeatability (at 5% load)	0.0125 mg	0.0125 mg	0.0125 mg
Linearity deviation	0.06 mg	0.06 mg	0.06 mg
Sensitivity offset (at nominal load) ▲	0.2 mg	0.25 mg	0.4 mg
Minimum weight (USP, tolerance = 0.10%) ▼	25 mg	25 mg	–
Minimum weight (tolerance = 1%) ▼	2.5 mg	2.5 mg	2.5 mg
Settling time	2 s	2 s	2 s
<b>Dimensions and other specifications</b>			
Balance dimensions (W × D × H)	222 × 379 × 353 mm	222 × 379 × 353 mm	222 × 379 × 353 mm
Weighing pan dimensions (W × D)	–	–	–
Weighing pan diameter	80 mm	80 mm	80 mm

▲ after adjustment with internal weight

▼ determined at 5% load, k = 2

All models are available as approved versions.



	MX104	MX204	MX304
<b>Limit values</b>			
Capacity	120 g	220 g	320 g
Readability	0.1 mg	0.1 mg	0.1 mg
Repeatability (at 5% load)	0.1 mg	0.1 mg	0.1 mg
Linearity deviation	0.2 mg	0.2 mg	0.3 mg
Sensitivity offset (at nominal load) ▲	0.5 mg	0.8 mg	1 mg
<b>Typical values</b>			
Repeatability (at 5% load)	0.05 mg	0.05 mg	0.05 mg
Linearity deviation	0.06 mg	0.06 mg	0.06 mg
Sensitivity offset (at nominal load) ▲	0.3 mg	0.5 mg	0.6 mg
Minimum weight (USP, tolerance = 0.10%) ▼	100 mg	100 mg	100 mg
Minimum weight (tolerance = 1%) ▼	10 mg	10 mg	10 mg
Settling time	2 s	2 s	2 s
<b>Dimensions and other specifications</b>			
Balance dimensions (W × D × H)	222 × 379 × 353 mm	222 × 379 × 353 mm	222 × 379 × 353 mm
Weighing pan dimensions (W × D)	–	–	–
Weighing pan diameter	90 mm	90 mm	90 mm

▲ after adjustment with internal weight

▼ determined at 5% load, k = 2

All models are available as approved versions.

## Features

### Performance

- MonoBloc weighing cell
- FACT automatic internal adjustment

### Efficient Operation

- 7" touchscreen
- 8 built-in applications
- Statistical data analysis
- Ergonomic door operation
- Backlit draft shield

### Quality Assurance

- OIML/NTEP approved
- User management
- Leveling assistant
- Configurable sample and task IDs
- Activity log
- StatusLight
- Configurable routine tests

### Data Management

- 3 interfaces: USB-A, USB-C, Ethernet
- Bluetooth option
- Advanced reporting

- Drop-to-cursor
- MT-SICS
- EasyDirect Balance software

### Sustainable Value

- Full metal housing
- Overload protection
- Power-saving mode
- Easy-to-clean QuickLock draft shield

## Accessories

Enhance performance, improve ergonomics, and handle your data efficiently with our wide range of accessories, including EasyDirect Balance data management software, printers, weights, density kit, and Bluetooth adapter.

For further information on accessories, please visit our web page.

► [www.mt.com/lab-accessories](http://www.mt.com/lab-accessories)



**Mettler-Toledo GmbH**  
Im Langacher 44  
8606 Greifensee, Switzerland  
[www.mt.com/contact](http://www.mt.com/contact)

Subject to technical changes.  
© 10/2023 METTLER TOLEDO. All rights reserved.  
30839974A en  
Group Marketing

[www.mt.com/MX-analytical](http://www.mt.com/MX-analytical)

For more information



30839974